


Product Datasheet



LAB-85GS/P

Emergency Eye/Face Wash - *Plumbed in Laboratory*

Pedestal-mounted eye/face wash with integral powder coated stainless steel bowl which meets the requirements of the European Standard EN 15154 for Laboratories. Dust covers protect the twin spray nozzles from contaminants and are lifted off by the water jets upon operation. The eye wash diffusers are fitted with fine mesh strainers and individual flow controllers and are designed to give a gentle flow of aerated water.

Specifications

MATERIALS OF CONSTRUCTION	
PIPEWORK & FITTINGS (GS)	Stainless steel with 150lb medium wall tubulars & fittings
OPERATING VALVE	Stainless steel
EYE/FACE WASH BOWL	Powder coated stainless steel
EYE WASH DIFFUSERS	Chrome plated brass with stainless steel mesh
STAINLESS STEEL - STANDARD FINISH	Green powder coated polyester finish
SERVICES	
WATER INLET	1" Male BSP
DESIGN OPERATING PRESSURE	2.0 to 6 BAR G (29 to 87 PSI) (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	Eye/face wash: 12 litres/minute minimum (3 US Gallons)
ENVIRONMENTAL OPERATING TEMPERATURE	
MINIMUM AMBIENT OPERATING TEMPERATURE	5° C (41° F)
MAXIMUM AMBIENT OPERATING TEMPERATURE	35° C (95° F)
ACTIVATION/OPERATION	
EYE/FACE WASH	Push plate operated (Optional treadle foot control for hands free operation)
WEIGHTS and DIMENSIONS	
DIMENSIONS (WxDxH)	429mm (16.9in) x 547mm (21.5in) x 1110mm (43.7in)
WEIGHT	8kg (18lbs)

View our Guide to the ANSI/ISEA Z358.1-2014 International Standard for Emergency Eyewash and Shower Equipment at www.hughes-safety.com

HUGHES



HUGHES-SAFETY.COM

Justrite Safety Group

www.hughes-safety.com

LAB-85GS/P

Emergency Eye/Face Wash - Plumbed in Laboratory

