

Product Datasheet

Heated Cabinet for use with the STD-68G

Heated cabinet intended for use with the STD-68G self-contained eye/face wash unit when positioned in locations where frost protection is required.

- Suitable for use in ambient temperatures down to -10C
- Eye wash unit can be filled while inside the cabinet via the drop down access panel
- Optional tamper proof fastenings on door and fill panel which snap in the event of an emergency or to refill
- Wall brackets included



Specifications

MATERIALS OF CONSTRUCTION	
ENCLOSURE	Glass Reinforced Plastic (GRP) with foam insulation
COLOUR	White with green/white safety stripes and eye wash sign
SUPPORT BRACKET	Stainless-steel
SERVICES	
ELECTRICAL SUPPLY	110-265 VAC Max
THERMOSTAT SET POINT	+15C / +59F to +5C / +41F
INRUSH CURRENT	2.5A@50W
DIMENSIONS & WEIGHT	
DIMENSIONS - (HxWxD)	839mm (33in) x 680mm (26.8in) x 544mm (21.4in)
WEIGHT (NO OPTIONS)	Empty cabinet: 20kg Including STD-68G filled with water: 80kg

General Arrangement Drawing

Heated Cabinet for use with the STD-68G

