Inline water heated pedestal mounted eye wash with ASA closed bowl STD-IH-45GS/P

Suitable for indoor use where there is no hot water supply. Built for non-hazardous areas, this heated eye wash ensures the delivery of tepid water.

The integral acrylic capped ASA lid connects to the water valve for automatic operation when the lid is pulled down. The eye wash unit has a flow rate of 8 - 11.4 litres per minute. Meets EN15154 and ANSI Z358.1-2014 standards.




Specifications


MATERIALS OF CONSTRUCTION	
PIPEWORK	Stainless steel
BOWL/LID	ASA
DIFFUSERS	Aerated & laminar flow. Plastic diffuser, chrome plated brass retainer
STANDARD FINISH	White with green pictogram sign
SERVICES	
WATER INLET	15mm compression or ½ inch BSP
OPERATING PRESSURE	Aerated flow minimum pressure 3.5 BAR G to 6 BAR G Laminar flow minimum pressure 2 BAR G to 6 BAR G
MINIMUM FLOW RATES	Eye wash: 8 - 11.4 L per minute / 3 US gal per minute
HEATING TYPE	Inline water heater
HEATING LOAD	11-13.5kw
ELECTRICAL EQUIPMENT	Non-flameproof
ELECTRIC SUPPLY	400V Three Phase
OPERATION	
EYE/FACE WASH	Pull down lid
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	340mm (13.4in) x 464mm (18.2in) x 1211mm (47.7in)



Inline water heated pedestal mounted eye wash with ASA closed bowl


STD-IH-45GS/P







FIXING DETAIL SCALE 1:8





www.hughes-safety.com