Eye wash diffuser kit for STD-45G

Part No. 01 02 075 12984

Hughes recommend replacing eye wash diffusers every 6 months to ensure correct functionality of the unit throughout its lifetime.

What's included in the kit:

- x10 aerated diffusers
- Diffuser key for ease of replacement





Specifications

MATERIALS

EYE WASH DIFFUSERS

COMPATIBLE WITH THE FOLLOWING MODELS

Rubber seal Plastic diffuser body Stainless steel filter Chrome plated brass retaining ring *Eyewashes:*

STD-45G STD-45G(S)/P EXP-EJ-45G(S)/P EXP-AH-45G(S)/P Combination Showers: EXP-18G(S)/45G EXP-AH-5G(S)/45G STD-TC-100KS/45G EXP-SD-18G(S)/45G EXP-20G(S)/45G EXP-33G(S)/45 Cubicle Showers: STD-SD-32K/45G STD-SD-31K Mobile Showers: STD-40K/45G STD-J-40K/45G STD-H-40K/45G



Replacing the eye wash diffusers:

- Use the diffuser key to remove the existing diffusers in an anti-clockwise direction
- Clean any dust or debris from the area
- Fit the new diffusers using the diffuser key, taking care not to overtighten





www.hughes-safety.com