Floor mounted laboratory safety shower with eye wash L18GS34G

Suitable for laboratories and general light duty indoor use, this combination emergency safety shower and eye/face wash meets the demands of ANSI Z358.1-2014. The powder coated stainless steel construction protects against corrosive and flammable substances and is easy to clean when sterilizing the lab environment.




Specifications

MATERIALS OF CONSTRUCTION	
PIPEWORK & FITTINGS	Stainless steel
OPERATING VALVE	Stainless steel
SHOWER ROSE	Powder coated stainless steel
EYE WASH BOWL	Powder coated stainless steel
EYE WASH DIFFUSER	Chrome plated brass retaining ring, stainless steel filter mesh, plastic body
STANDARD FINISH	Green powder coated polyester
SERVICES	
WATER INLET	1" male NPT
OPERATING PRESSURE	2 to 6 BAR G / 29 to 87 PSI (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	Shower: 76 L per minute / 20 US gal per minute
	Eye wash: 12 L per minute / 3 US gal per minute
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C / 41F
MAXIMUM	35C / 95F
OPERATION	
SHOWER	Pull handle
EYE WASH	Push plate
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	320mm (12.6in) x 815mm (32.1in) x 2300mm (90.6in)
WEIGHT	15kg (33lb)



Floor mounted laboratory safety shower with eye wash

L18GS34G





www.hughes-safety.com

Hughes Safety Showers Ltd, 457 Campbell Street, Sarnia, Ontario N7T 2J1 Canada T: 1-866-312-1652 E: customer.service@hughes-safety.com