## Pedestal mounted eye wash with stainless steel open bowl

## 85GP 85GSP

Eye/face wash facilities must be situated within 10 seconds reach of a hazard, such as the risk of a chemical spill. This pedestal mounted eye/face wash unit is quick and simple to activate in the case of an emergency. The protective dust covers lift off when the push plate is activated allowing the aerated diffusers to provide 3 US gallons per minute of water for a thorough decontamination.

Meets the requirements of ANSI Z358.1-2014.




## Specifications

MATERIALS OF CONSTRUCTION	
PIPEWORK	Stainless steel (GS) or galvanized mild steel (G)
BOWL/LID	Stainless steel
DIFFUSERS	Chrome plated brass retaining ring, stainless steel filter mesh, plastic body
STANDARD FINISH	Polished brush (GS) or green powder coated (G)
SERVICES	
WATER INLET	1 <sup>1</sup> / <sub>4</sub> " Female NPT
OPERATING PRESSURE	2 to 6 BAR G / 29 to 87 PSI
	(higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	12 L per minute / 3 US gal per minute
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C / 41F
MAXIMUM	35C / 95F
OPERATION	
EYE/FACE WASH	Push plate
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	314mm (12.4in) x 535mm (21.1in) x 1154mm (45.4in)
WEIGHT	10kg / 22lb



## Pedestal mounted eye wash with stainless steel open bowl

85GP 85GSP





www.hughes-safety.com

Hughes Safety Showers Ltd, 457 Campbell Street, Sarnia, Ontario N7T 2J1 Canada T: 1-866-312-1652 E: customer.service@hughes-safety.com